


DATA SHEET



S4LFT0063/121 standard F-Theta

- for 532 nm
- optical glass
- standard coating



outline drawing

Sill Optics
GmbH & Co. KG
Johann-Höllfritsch-Straße 13
D-90530 Wendelstein

Copyright © Sill Optics GmbH & Co. KG
All rights reserved.
Issue E
Published: 2.02.2018

Tel.: +49 (0) 9129 9023 0
Fax: +49 (0) 9129 9023 23
E-mail: info@silloptics.de
Web: www.silloptics.de

All information contained in this data sheet is for information purposes only and is not binding. The content is subject to change at any time without notification, all information without guarantee. We reserve the right to make constructional changes in the course of product improvement.


DATA SHEET



specifications

article number	S4LFT0063/121
design wavelength [nm]	532
effective focal length [mm]	62.9
max. entrance beam-Ø [mm]	7.0
optical scan angle [±°]	19.6
scan length [mm] (1 mirror system)	42.5
aperture stop distance [mm]	15
working distance [mm]	75.7
scan area for a 2 mirror system with mirror distance from lens housing for mirror 2 / mirror 1	30 x 30 10.0 / 20.0
max. telecentricity error [°]	4.5
total transmission [%]	> 97
lens material	optical glass
LIDT (coating)	2.5 J/cm ² per 1ns pulse at 50Hz 2.5 MW/cm ² cw
SP and USP usable [✓/×]	×
weight [kg]	0.22
cover glass	S4LPG0105/121
accessory	S4MEC3985 - M39 to M85

spot



- spot radius in μm at 86% level for a Gaussian laser beam ($M^2=1$) with 7 mm diameter at $1/e^2$, clipped at $1/e^2$
- field size and mirror distances as given above for a 2 mirror scan system
- PRAM parameters: mechanical mirror scan angle

notes

The aperture stop given is the point where the scan mirrors should be placed symmetrically around in order to reach best performance. In a 1 mirror system it is the position of the scan mirror.
Aperture stop distance = front focal point in telecentric f-theta lenses

The calculations of the scan length and scan areas of our f-theta lenses are based on the geometric design of typical scan systems with a certain mirror spacing. The values given assume a vignetting of less than 1%. If used with non-typical scan systems or with scan systems which have been designed for larger or smaller laser beams, different scan lengths and scan areas will result.

Effective focal length and working distance have a tolerance of +/- 1.5%
Graphs given by design

LIDT = Laser Induced Damage Threshold, valid for the coating at design wavelength and gaussian intensity profil
General LIDT for lenses without SP/USP compatibility (short pulse or ultra short pulse) can be lower, depending on material and internal reflections.